



QUOTATION

Siddons-Martin Emergency Group
Don Hoyt

Exp. Date: 06/01/2022
 Quote No: 10090-0001
 METROMEDIC: MM 1146/53 RR MM 1146/153 Mod
 INFO: SPEC_MM RR-MetroMedic Boilerplate
 METROMEDIC: RR-1146-53 RR MM-Type 1 146/153 Module
 EMS EQUIP: EMS-LOOSE Factory Ship Loose - EMS Equipment

05/04/2022 11:18:57

Page 1

ID	PART NO	S	DESCRIPTION	QTY
REV			== RR-MetroMedic Boilerplate - 1.026 04/05/22 ==	1
REV			INFORMATION	1
REV	00-01-0999		RR, Information - Scope, Purpose and Classification	1
REV	00-01-4117		Manufacturer Certified ISO 9001	1
REV			WARRANTY	1
REV	00-02-8780		MD, Warranty, Conversion, 12 Month	1
REV	00-02-8785		MD, Warranty, Paint, 60 month Prorated, Standard	1
REV	00-02-8790		MD, Warranty, Limited Electrical	1
REV	00-02-8795		MD, Warranty, Cabinet Construction	1
REV			== RR MM-Type 1 146/153 Module - 1.026 04/05/22 ==	1
REV			CERTIFICATIONS REQUIRED	1
REV	00-05-0050	<	This unit built in accordance with KKK-A-1822-F in effect on the date of order with exceptions as noted herein.	1
REV	00-05-0100	<	MD, This unit built in accordance with KKK-A-1822-F CN 10 Cabinet Requirements This unit as specified meets all requirements of KKK-A1822-F Change notice 10. All cabinets shall be labeled as to their capacity Rating.	1
REV			01- CHASSIS REQUIREMENTS	1
REV			FORD CHASSIS	1
REV	01-01-2223	< >	MD, 2022 Ford F-350, 4x2, 6.7L, 169" WB 2022-7 Auto throttle OEM Ford Dual Alternators OEM Ford Mirrors, OEM, Heated/Remote Cab seats OEM 40/20/40 split bench (Center removed) New for 2020- Sync 3 Enhanced voice recognition communication and entertainment system 8" LCD Capacitive Touch screen in center stack w/swipe Capability Pinch to Zoom capability AppLink 911 assist Apple carPlay and Android Auto Smart-charging USB-C Ports (2)	1
REV	01-02-0100		Domestic Chassis	1
REV			ALTERNATORS	1
REV	01-03-1001		Alternator - Standard OEM	1
REV			SUSPENSION	1

ID	PART NO	S	DESCRIPTION	QTY
REV	01-07-3001		Rear Suspension, OEM Springs	1
REV			HIGH IDLE	1
REV	01-13-1675		High Idle Controls, OEM	1
REV			FRONT END ALIGNMENT	1
REV	01-17-7501		Front End Alignment, None- QC Check -Standard	1
REV	01-19-0002	<	RR, Road Rescue Stainless Grille Logo, with Diamond grade Blue reflective backin	1
			Blue Diamond grade Reflective behind cut out.	
REV			OUTSIDE REAR VIEW MIRRORS	1
REV	01-20-0104		Mirrors, OEM-STD	1
REV	01-21-4600		MD, Cab Flooring, Black Rubber, F350/450, OEM	1
REV			WHEEL COVERS	1
REV	01-24-2111	< >	MD, Wheel Covers, Phoenix, F350, Installed with Air Max Valve Extenders, std	1
REV			BASE CONVERSION	1
REV	01-45-0203		MD, Conversion, Type 1, 153 Module, F350 4x2 22-1	1
REV			MODULE BODIES:	1
REV	02-01-2120		MD, Interior Headroom, 67 inches	1
REV	02-01-3114	<	MD, Module, Type 1, 153" Body Length, Duraseam Doors, 153" L x 95" W	1
REV	02-01-3152		MD, Body Width 95" Standard	1
REV	02-01-9564	<	MD, Aisle Space, 50", Type 1 (49-50" actual)	1
			Requires stainless steel wheel well covers attached to squad bench and base wall cabinets that will protrude up to 1.5" into aisle way on each side.	
REV			STRUCTURAL FRAMING - RFP	1
REV	03-01-1501		MD, Type 1, General Body Construction Spec	1
REV	03-01-1503		MD, Type 1, Vehicle Body Structure Spec	1
REV			EXTERIOR MODULE CONSTRUCTION	1
REV	03-03-1040	>	MD, Stone Guard, Front, Diamond Plate, Type 1, Standard Height	1
REV			FUEL FILLS & SPLASH PLATE	1
REV	03-03-8030	>	MD, Housing Fuel Fill, Cast Aluminum, Type 1	1
REV			DEF FILL HOUSING AND SPLASH PLATE	1
REV	03-03-8615		MD, DEF Fill, Housing, For Ford F series	1
REV			REAR KICKPLATE	1
REV	03-03-9101	<	MD, Rear Kick plate, W/Tag Recess, No Light Holes, Duraseam No Under-Ride Bumper	1
REV			SUB-FLOOR SYSTEM	1
REV	03-04-0168	>	MD, Floor, Interior, Non Wood, Thermolite, Type 1	1
REV			MODULE ENTRANCE	1
REV	03-05-0200		MD, Module Access, CS Door standard location	1
REV			MODULE DOORS, HANDLES & HOLD OPENS	1
REV	03-06-0713	< >	MD, Hold Open Rear Entry Doors, (2) 5.5" Cast Grabber - Installed so doors will open as wide as possible - Mount at Bottom of doors.	1
REV	03-06-0817	<	MD, Hold Open - Gas Strut, Curb Side Entry Door, 35# New Code Per ECN 1823	1
REV			ENTRY DOOR INNER PANELS	1
REV	03-06-7231	< >	MD, Entry Door Panels, Durasafe, Stainless Steel, w/ Center Chevrons - Durasafe Design	1

ID	PART NO	S	DESCRIPTION	QTY
			- Aluminum Center Panels covered: white/red reflective tape	
REV			SIDE DOOR STEP	1
REV	03-08-2112		MD, Side Entry Step Well, Type I, Aluminum Diamond Plate	1
REV	03-08-3052	>	MD, Light, Side Entry Step well, Peterson, M126c	1
REV			WINDOWS	1
REV	03-09-4109	>	MD, Window, Upper, CS/Slider, Rr/Fixed, Privacy Tint, PAN	1
REV			MODULE TO CHASSIS MOUNTING SYSTEM	1
REV	03-10-1210		MD, Module to chassis mounting system, Type I	1
REV			CAB TO MODULE	1
REV	03-11-2502	< >	MD, Bellows, Pass thru, Unigrip, F1 2008+, With Aluminum cab insert.	1
REV			REAR BUMPER AND REAR STEP CONSTRUCTION	1
REV	03-12-2503	<	MD, Rear Bumper w/ Skids & Flip Up, F1/C1, w/LED DOT lights w/ Gator Grip on flip up step.	1
REV	03-12-2550	<	MD, Coating, Polyurethane, Rear Bumper Supports Black	1
REV			INSULATION	1
REV	03-13-3006		MD, Insulation, Walls and Ceiling, R11 Fiberglass Batt	1
REV			RUB RAIL AND FENDER RINGS	1
REV	03-15-6651	<	MD, Rub Rails, Skirt Line, Extruded "C" channel (E-one Style) NO REFLECTIVE INSERT.	1
REV	03-15-8356	>	MD, Fender Flare, Bright Finish	1
REV			SPLASH GUARDS AND RUNNING BOARDS	1
REV	03-16-1850	<	RR, Mud Flaps, Rear, Black w/ Road Rescue Logo, MM Heavy Duty Rubber Mud Flaps to be bolted to the wheel liner behind the rear duals with 1/4" x 20 Stainless Steel bolts, washer and nylon locknut for ease of maintenance and repair	1
REV	03-16-3603		MD, Running Boards, F350, w/Gator Grip	1
REV			DRIP RAILS	1
REV	03-17-1020		MD, Drip Rail Trim Moldings Over Door Openings	1
REV			CAB TO PATIENT AREA ACCESS	1
REV	03-19-2301		MD, Bulkhead, Unigrip, Type 1F/D, Pass Thru, w/ Sliding Lexan Window	1
REV			LICENSE PLATE HOLDER	1
REV	03-20-4050	<	MD, License Plate Holder, Cast, LP0002-1, STD - in rear kick plate, centered License holder comes with (2) LED lights.	1
REV			EXTERIOR COMPARTMENT CONSTRUCTION	1
REV	04-01-0502	< >	MD, Exterior Compartment, Std, Floor 2.5" Drop Down from Door Opening, Each compartments #2, #4, #6 and #6.5 are STD drop down floor	4
REV	04-01-0504	< >	MD, Exterior Compartment, Sweepout, Each - Compartments #1 and #8 are standard sweep out	2
REV	04-01-3017	<	MD, Door Sill Protector, Stainless, All Compts Door Sill Protection - Install Stainless Steel sill protector on lower edge of all door frames to prevent paint damage	1

ID	PART NO	S	DESCRIPTION	QTY
REV	04-01-5106	<	MD, Polyurethane Coating per compartment light gray	6
REV			EXTERIOR COMPARTMENT DOORS	1
REV	04-02-0602	>	MD, Compartment Handle, Trimark Chrome/Black, Locking Paddle, Curbside	4
REV	04-02-0604	>	MD, Compartment Handle, Trimark Chrome/Black, Locking Paddle, Streetside	3
REV			COMPARTMENT DOOR HOLD OPEN	1
REV	04-02-7751	< >	MD, Hold Open, Gas Strut, Ext Compt, 60lb for comp. #4 hold open	1
REV	04-02-7753	<	MD, Hold Open Gas Strut, Ext Compt, 30lb Compartments 1, 2, 6, 6.5	4
REV	04-02-7757		MD, Hold Open, Gas Strut, RF Compt, 30lb	1
REV			COMPARTMENT LIGHTING	1
REV	04-03-1480	< >	MD, Compartment Light, 2" Incandescent, Each Compartment	7
			1 - access panel on wall 1 2 - Wall #1 below electrical shelf if optioned 4 - Wall #3 in access panel 6 - Ceiling centered 6.5 - Wall #3 8- Wall #3 in access panel and the O2 light in comp 1	
REV			COMPARTMENT #1 - STREETSIDE FWD	1
REV	04-06-0450	<	MD, Compartment #1, 3/4 High (On type III - includes recess for stair chair storage)	1
REV	04-06-0475	<	MD, With Dogleg for Stair chair in Compartment #1, (not available when electric O2 rack is selected) (this will decrease space for attend seat & cot by 5.25") for stair chair	1
REV			COMPARTMENT #2 - STREETSIDE FWD WHEELWELL	1
REV	04-07-2140		MD, Compartment #2, 50" Aisle, Standard Configuration	1
REV	04-07-2630	<	MD, Compartment #2, Shelf, Fixed, Electrical storage, w/ Divider Area to right of divider will be used for bio-waste in A/A if selected. If no bio-waste, area to be left open for additional customer storage.	1
REV	04-08-2100	>	MD, Compartment #3, NONE	1
REV			COMPARTMENT #4 - STREETSIDE AFT	1
REV	04-09-3245		MD, Compartment #4, 3/4 Height.	1
REV	04-09-4550	>	MD, Compartment #4, Shelf, Adjustable, w/Aluminum Track, First Shelf	1
REV			COMPARTMENT #6 - CURBSIDE AFT	1
REV	04-11-1097		MD, Compartment #6, Full Height	1
REV	04-11-2090	<	MD, Compartment #6, First Divider, Vertical, 3/16" Thick, Recessed Adj Track (divider to be full depth if a shelf is requested) centered.	1
REV	04-11-4652	< >	MD, Compartment #6, Equipment Strap, Seat Belt Style, Each Nylon web strap w/ seat belt buckle and two (2) footman loops	1
REV			COMPARTMENT #6.5 - CURBSIDE AFT WHEELWELL	1
REV	04-12-0131		MD, Compartment #6.5, Below Squad Bench Floor Level	1
REV			COMPARTMENT #8 - CURBSIDE UPPER FORWARD	1
REV	04-14-2120	>	MD, Compartment #8/8.5, Single Door	1

ID	PART NO	S	DESCRIPTION	QTY
REV	04-14-8010	< >	MD, Compartment #8, Shelf, Adjustable, RF Cabt, First shelf w/Aluminum Track (1) RF Comp "8"/cabinet "U8" area, centered.	1
REV	04-14-8015	< >	MD, Compartment #8, Shelf, Adjustable, Additional, for Aluminum Track, Each RF Comp "8"/cabinet "L8" area, centered.	1
REV			INTERIOR TRIM AND FEATURES	1
REV	05-01-0106	< >	MD, Interior Cabinets, Duralite Construction, Thermalite, CN10 Compliant Circuit board mounting board will be made of PVC	1
REV			INTERIOR ADJUSTABLE SHELVES	1
REV	05-02-0052	>	MD, Shelf, Interior, Non-Wood, (1) Adjustable, in Cabinet:	4
REV	05-02-0054	< >	MD, Shelf Track, Cabinet, #HA24663, CN 10 Upgrade ("C" channel/exterior shelf style track)	4
			This option may require quantity adjustment	
REV			HEADLINER	1
REV	05-06-2705	>	MD, Headliner - Flat, Expanded PVC, Std	1
REV			FLOORING	1
REV	05-07-0120	< >	MD, Flooring, Lon Seal "Lonplate II " With approximately 3" roll up both street side and curbside.	1
REV	05-07-0121		MD, Color, Gunpowder Gray #424TX	1
REV	05-07-9897		MD, Floor, Thresholds, .063 Aluminum , Painted w/Black Poly-urea coating	1
REV			Entry Door Grab Handles	1
REV	05-10-1529	<	MD, Entry Door Grab Handles (3), Custom "L" Shape, 1", Yellow - Yellow Powder Coat Finish Stainless Steel Grab Handles	1
REV			Ceiling Grab Rail - Center	1
REV	05-10-1933	<	MD, Ceiling Grab Rail, Overhead, 84", 1" Diameter Handicap Style, Yellow Yellow Powder Coat Finish	1
REV			IV FLUID HANGERS	1
REV	05-11-0015	>	MD, IV Hook, Perko Snap Hook w/Velcro Strap, Each	2
REV			ACTION WALL AREA #2	1
REV	05-13-3086		MD, Cabinet, A/A, 50" Aisle, No Bio waste, Rounded corners	1
REV	05-13-4322	< >	MD, Tray, A/A, 50" Aisle, No Bio waste, Poured, Gray **only for 50" aisle space units**	1
REV	05-13-4402		MD, AA Upper Cabinets, U2.5 Angled, U2 , U1, 3/4H Comp #1	1
REV			CABINET DOORS	1
REV	05-13-4492		MD, Doors, U1 Gray Poly carbonate Slider, CN 10 Compliant	1
REV	05-13-4510		MD, Door, U2 Gray Poly carbonate Slider, CN 10 Compliant	1
REV	05-13-4522	< >	MD, Door, U2.5 , Hinged Wood Hinged on Right.	1
REV			Interior Streetside #3 - CPR Seat	1
REV	05-14-1532		MD, CPR side seat, Fixed Backrest	1
REV	05-14-1534	<	MD, CPR, Lid, Hinged Flip Up With Trimark Latch	1
REV	05-14-1547		MD, Cabinet U3.5	1
REV	05-14-1577		MD, Cabinet C3.5, deleted For Telemetry Area	1
REV	05-14-1587		MD, Cabinet L3.5, full height, std	1
REV	05-14-4418	<	MD, "U" Barrier Bar, Padded, 1.5" SS, CPR Seat, Gunmetal Mounted at the front of the CPR side seat vertically in line with the Padded head cushion on the upper AA cabinets.	1

ID	PART NO	S	DESCRIPTION	QTY
REV	05-14-4552		MD, Telemetry Tray, Poured, Gray	1
REV			CABINET DOORS	1
REV	05-14-4592		MD, Doors, U3.5 Gray Poly carbonate Slider, CN 10 Compliant	1
REV	05-14-4650		MD, Doors, L3.5, Gray Poly carbonate Slider, CN 10 Compliant	1
REV			STREETSIDE REAR AREA #4	1
REV	05-15-5050		MD, Cabinet U4	1
REV	05-15-5112		MD, Cabinet C4, Inside/Outside Access	1
REV	05-15-5118		MD, Cabinet L4, Deleted	1
REV			CABINET DOORS	1
REV	05-15-6115		MD, Doors, U4 Gray Poly carbonate Slider - CN 10 Compliant	1
REV	05-15-6127		MD, Doors, C4, Gray Poly carbonate Slider - CN 10 Compliant	1
REV			SQUAD BENCH AREA	1
REV	05-16-0049	>	MD, Squad Bench, Bio-Waste @ Head	1
REV	05-16-0075	<	MD, Lid, Squad Bench, Single W/Bio-Waste Must use M1 latch for CN 10 on bio waste door	1
REV	05-16-0080		MD, Handle, Trimark, CPR Seat, Std.	1
REV	05-16-0082		MD, Handle, Trimark, Squad Bench, STD	1
REV	05-16-0094		MD, Strut, Gas, 30 LB, Installed	1
REV	05-16-0214	<	MD, Seatbelt, Assy, (4 Point), Per 4Max, Black, Vert. Mount, (1) Each, CN-8 Above bench Lid mounting (1) for CPR side seat (Delete shop note if not required) (2) for squad Bench	1
REV	05-16-0214	<	MD, Seatbelt, Assy, (4 Point), Per 4Max, Black, Vert. Mount, (1) Each, CN-8 Above bench Lid mounting (1) for CPR side seat (Delete shop note if not required) (2) for squad Bench	2
REV	05-16-0222		MD, Patient Restraint Belts, Squad Bench (3)	1
REV			CURBSIDE REAR	1
REV	05-16-9923		MD, Cabinet, Curbside Rear, Standard	1
REV	05-17-2508	< >	MD, Cabinet, Glove Box Holder, (3), Above C/S door, Must use M1 latches for KKK Change notice 10 compliance	1
REV			CURBSIDE RIGHT STACK STORAGE #8	1
REV	05-18-0035		MD, RF ALS, Split Upper/Lower, HVAC at Top	1
REV	05-18-5158		MD, Doors, RF, U8, Dual Gen III OHO, Poly carbonate Doors, Gray	1
REV	05-18-5354		MD, Doors, RF, L8, Dual Gen III OHO, Poly carbonate Doors, Gray	1
REV			ATTENDANT SEAT	1
REV	05-19-6802		MD, Attendant's Seat, EVS 1780 "Comfort" Hi-Back w/Per4Max belting	1
REV	05-19-6804	>	MD, Color, Gunmetal, Per4Max Belt, Black	1
REV	05-19-7215	< >	MD, Attendant's Seat Base, EVS CBS Box Style Box opening to be toward Rear access door	1
REV			INTERIOR COLORS	1
REV	05-20-0015		MD, Mica, Light Gray Gloss	1
REV			UPHOLSTERY	1
REV	05-20-5918	>	MD, Upholstery Color, Gunmetal	1
REV			CABINET LATCHES- INTERIOR	1
REV	05-21-8213	< >	MD, Latch, Southco M1, 2" S/S, (3/4" door) Non-Locking, CN 10-Rated 10lb (self latching) Flush Mount. Non-Locking	1
REV	05-21-8213	< >	MD, Latch, Southco M1, 2" S/S, (3/4" door) Non-Locking, CN 10-Rated 10lb (self latching) Flush Mount. Non-Locking	1
REV	05-21-8219	< >	MD, Latch, Southco M1, 2" S/S, (3/8" Door) Non-Locking, CN 10-Rated 10lb (self latching) Flush Mount. Non-Locking	2

ID	PART NO	S	DESCRIPTION	QTY
REV			GENERAL WIRING	1
REV	06-01-0130		MD, Electrical System: Printed Circuitboard	1
REV	06-01-0250		MD, Vanner, "E" Spec, PC Board, No LB	1
REV			COMMUNICATION	1
REV	06-06-5538	< >	MD, Coax Cable, RG58/U, Each, Terminate: (1) - From module roof Dome #3 to behind passenger seat with 6' pigtails	2
			(1)- From module roof port Dome #7 to behind the passenger seat Standard - with 6' pigtails	
REV	07-00-0610	<	MD, Light, in Circuit Board Area, for Electrical Troubleshooting - with integral switch; wired constant hot.	1
REV			POWER SOURCES	1
REV	07-01-1002	<	MD, Power Source, 12VDC, 20A, Ignition/Shoreline Hot 20amp 12 volt DC circuit ran to two locations, (1) pre-wire coil and tagged in action area and (1) pre-wire coil and tagged behind driver's seat.	1
REV	07-01-1008	< >	MD, Power Source, 12 VDC, 15 Amp (+-), Ignition Hot - Ignition hot, terminating in cab console - with 6 foot tails (hot and ground).	1
REV	07-01-1016	< >	MD, Power Source, 12 VDC, 30 Amp (+-), Constant Hot - Constant Hot, to terminate behind the passenger seat - with 6 foot tails (hot and ground).	1
REV			VOLTMETER	1
REV	07-02-1155	<	MD, Alarm, Low Voltage, Audio/Visual Light in cab console and Buzzer in cab.	1
REV	07-02-1157		MD, Voltmeter, Glowshift, Digital	1
REV			BATTERY SYSTEM	1
REV	07-04-8721	<	MD, Battery Sw, 5min Timer, F1, Fig 5B, Batt under Hood Activated thru OEM ignition switch timer function upon ignition "off". Momentary rocker switch, on driver's side of cab console, to function as timer shutoff and also reactivate timer. (2) OEM batteries under hood ONLY Module power is turned on/off. Chassis power is NOT turned off.	1
REV	07-09-1007	<	MD, Battery Charger, Conditioner, Progressive Dynamics, PD9130 Charger/Conditioner mounted in Comp "E"	1
REV			12VDC OUTLETS	1
REV	07-10-1101	< >	MD, Outlet, Power Point Style, (2), A/A - on standard 20-amp ignition hot circuit. ("elect battery switch")	1
REV	07-10-1109	<	MD, Power Outlet, Kussmaul, USB Dual Port, 5VDC, 4.8 Amp, switch panel Located in the cab switch panel per Electrical Engineering	1
REV			FRONT CONSOLE	1
REV	08-01-3602		MD, Console, Center, Pass-thru, Mica Finish, F1, CN11	1
REV	08-02-0006	<	MD, Module Electrical Panels, Brushed Stainless Steel brushed stainless steel panels for the Outlet panels, switch panels and other faceplates in the MODULE only.	1

ID	PART NO	S	DESCRIPTION	QTY
REV			ATTENDANT CONTROL PANEL	1
REV	08-03-0303		MD, Console, A/A, Wood, Angled	1
REV			SIREN ELECTRONIC - CONTROL HEADS / AMPS	1
REV	09-03-1802	>	MD, Siren, Whelen, WS-295-SLSA1	1
REV			SIREN SPEAKERS	1
REV	09-03-2707	<	MD, Siren Speakers, Cast SAD/PSAD3827-20FSD-1, F-Series 2020 Thru Front Bumper	1
REV	09-03-3530		MD, Switch, Siren/Horn Thru Horn Ring	1
REV			BACK-UP ALARMS	1
REV	09-05-1112		MD, Back-up Alarm, No Cutoff Switch	1
REV			WARNING LIGHT FLASHERS	1
REV	09-80-2000	< >	MD, Flasher, Vanner 5860GCPE, C/D/E Spec Will flash 75FPM single flash ONLY	1
REV			WARNING LIGHTS	1
REV			LED Series - 900 SINGLE ROW (Flange Separate)	1
REV	09-95-1723	>	MD, Light, M9RC, LED, Whelen, Red, Clear Lens, Internal Flash, w/Flange	12
REV	09-95-1725	>	MD, Light, M9AC, LED, Whelen, Amber, Clear Lens, Internal Flash, w/Flange	3
REV	09-95-1729	>	MD, Light, M9C, LED, Whelen, Clear, Internal Flash, w/Flange	1
REV			LED Series - 700 (Flange Separate)	1
REV	09-95-4802	<	MD, Light, Whelen, LINZ6R, LED-Red with chrome flanges	2
			(2) front intersectors	
			(2) As Grille Lights	
REV	09-95-4803		MD, Light, Whelen, LINZ6R, LED-Red, W/Chrome Flange	2
REV	09-95-9390		MD, Housings, Cast, 15 degree angled, 7x3, Intersection, 2017+ F-series, Pair	1
REV	09-95-9393		MD, Housings, Cast, 500 Series, Upper Grille, Ford, 2020 F series, Pair	1
REV			EXTERIOR AUTOMOTIVE LIGHTING	1
REV	10-01-0048	<	MD, Taillight Pkg, Whelen, 600 LED Stop/Tail, Turn Arrow & Halogen Backup - Brake- Steady Burn - Turn Arrow – sequential arrow	1
REV			ICC/MARKER LIGHTS	1
REV	10-01-2175	<	MD, Light - Clearance, Whelen Mini OS, Amber LED, MetroMedic (5) - On front as clearance lights. (3) in the center (1) in each outboard corner (1) each side in upper front corner	7
REV	10-01-2176	<	MD, Light - Clearance, Whelen Mini OS, Red LED, MetroMedic . (5) - On rear as clearance lights. (3) in the center (1) in each outboard corner (1) each side in upper rear corner	7
REV			FLOOD AND LOAD SYSTEMS	1
REV	10-02-2202	<	MD, Light, Halogen, Whelen, 9H, Clear, 8-32 Deg - (2) each side as "Scene lights" - (2) on rear over rear doors as "Load Lights"	6
REV			11 - INTERIOR LIGHTING	1
REV	11-01-2800		MD, Lights, Weldon, 8046-0320-80, (4) S/S, (3) C/S	1
REV	11-01-9032	< >	MD, Timer, Momentary Switch, 15 Minute, Constant Hot (must have ECX timed battery switch with this option)	1
			Mount switch on C/S wall at the head of the squad bench in the standard location. Switch to allow activation and also deactivation. Wire to Streetside Domes in liner on High.	

ID	PART NO	S	DESCRIPTION	QTY
REV			SPOTLIGHTS / HANDHELD LIGHTS	1
REV	11-02-1003		MD, Handheld Spotlight - Sho-Me 200,000 CP	1
REV			ATTENDANT LIGHT	1
REV	11-03-2027	>	MD, Light, Optronics, 105500, 5 Inch, Each	1
REV			12 - ELECTRICAL 125 VOLT AC	1
REV			SHORELINE INLET	1
REV	12-01-9112	< >	MD, Shoreline, 20A, Super Auto Eject, White - with white cover; mounted above compartment "#2"	1
REV			OUTLETS - 125VAC	1
REV	12-02-2110	<	MD, Outlets, 125 VAC, Duplex, (1) Action Wall, (1) Right Front Cabinet - (1) outlet in action area - (1) outlet in the RF Cabinet "U8", wall #2, upper right.	1
REV			BLOCKHEATERS	1
REV	12-02-4001	<	Block Heater - With OEM Plug This option does not include a switch. (STANDARD).	1
REV			INVERTER - 125VAC	1
REV	12-03-1416		MD, Inverter, Vanner, IT12-2000, Pure Sine wave	1
REV			AUXILIARY ENVIRONMENTAL SYSTEMS	1
REV	13-02-0111		MD, Exhaust Fan, Single 12V, in Line Blower	1
REV			METROMEDIC HVAC UNITS	1
REV	13-02-5751	>	MD, Hoses, Heater, No Max, to Rear	1
REV	13-02-5774	< >	MD, Heat/AC, F1, Combo, w/Coolbar (new code) with thermostat in action area. 12vdc External Condenser, in Coolbar mounted on front of module. Painted to match front of module. Note: pick warning lights separately !!	1
REV	13-02-6027		MD, Air Conditioning Face Plate, Black Vinyl Clad	1
REV	13-02-6050	>	MD, Heat/AC Located RF corner, over ALS cabinet.	1
REV	13-02-6082	>	MD, Generation I, Steel Cool Bar cover	1
REV	13-02-7751	<	MD, Heat/AC manual switch if the Heat AC switch is already on in CAB Up position -Air conditioner Function Center position - Fan power only to blower fan Down Position - Heater function	1
REV			COT MOUNTING PROVISIONS	1
REV			Cot Mounts	1
REV	14-01-1514	<	MD, Cot Mount, Stat Track, Single Position, ST, 86", CN 8 Compliant Length of track is 86".	1
REV	14-01-4028		Center Mount	1
REV			OXYGEN AND AIR SYSTEMS	1
REV	14-02-2242	<	MD, O2 Cylinder Bracket, Multiversal, #QR-MV, W/ Straps (Uni-strut track mounting is now std) Specify O2 bottle size.	1

ID	PART NO	S	DESCRIPTION	QTY
REV	14-02-2244		MD, Track, Unistrut for Oxygen Rack	1
REV	14-02-3005		MD, Manual, O2 System	1
REV	14-02-3156	<	MD, O2 Regulator, Preset 50 PSI Ship Loose unless otherwise directed	1
REV	14-02-4153	< >	MD, O2 Outlets, Ohio Style (2 in Action Area, 1 CS Wall) (2) in Action Area, (1) CS wall above squad bench	1
REV	14-02-4920	>	MD, Lexan Flap, w/Hinge	1
REV			SUCTION SYSTEM	1
REV	14-03-3030		MD, Suction Pump, SSCOR 90206	1
REV	14-03-3045	>	MD, Suction Port	1
REV	14-03-3070	< >	MD, Suction System, SSCOR 23002 Disposable w/Canister Clip & Regulator NO Ohio style vacuum outlet - plumb hose from SSCOR canister through hole in AA wall panel Meets SAE J3043 Requirements	1
REV			MISC MEDICAL	1
REV	14-04-1200	< >	MD, Fire Extinguisher, 5# ABC with Surface Mount Brkt., Each HD Amerex Bracket #861H with Amerex 5LB fire extinguisher.	2
REV			PAINT AND FINISH	1
REV	15-00-0300		MD, MetroMedic Paint Process	1
REV	15-01-2000	<	Module Paint, Single Color, OEM White	1
			Ford white: FA91:YZ 2019 & up Dodge white : RAM88:GW7 Chevy G series white: FLNA40738 C3500- 5500 White FLNA 41383 International 4300-4400 white: NAV9212- Check chassis spec Freightliner white: CHA88:GW6-Check chassis spec	
REV	15-01-5000		Cab Paint - Single Color, OEM White	1
REV			PAINT STRIPING DESIGN	1
REV	15-02-1200		Paint Belt, None	1
REV			DECALS AND NOMENCLATURE	1
REV	15-05-0055	>	MD, Spare Tire, OEM only, Ship Loose	1
REV	74-09-0099	<	Indemnification Statement The purchaser agrees to defend, indemnify and hold Rev Ambulance Group harmless from any claims, costs (including actual attorneys' fees), damages and liabilities caused in whole or in part by any alteration or modification of, or changes or additions to the purchased products OR use of product for purposes it was not designed or intended for.	1
REV			End Of Order	1
REV			== Factory Ship Loose - EMS Equipment - 1.026 04/05/22 ==	1